



技術參數

整體數據表 – 個別數值取決於您的配置。

特性	值
授權	RCM Mark
Distributor type	2 to 1
預備狀態顯示	綠色LED
工作狀態顯示	黃色LED
Signal status display	黃色LED
附加功能	保持電流的降低
Cable identification	With inscription label holder Without inscription label holder
安裝類型	With through-hole for M2 screw 具配件
Electrical connection 1, function	Controller side
Electrical connection 1, connection type	電纜 插頭
Electrical connection 1, cable outlet	直的 Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101 M8x1, A-coded to EN 61076-2-104 開放式終端
Electrical connection 1, number of pins/wires	3 4
Electrical connection 2, function	Field device side
Electrical connection 2, connection type	2x 插座 2x cable
Electrical connection 2, cable outlet	直的 Angled Rotatable
Electrical connection 2, connection technology	Connection pattern ZB, self-tapping screw Connection pattern ZC, self-tapping screw Connection pattern ZC, metric screw Connection pattern H Plug pattern type A to EN 175301-803 Plug pattern type B to EN 175301-803 Plug pattern type B to industry standard, 11 mm Plug pattern type C to EN 175301-803 Connection pattern type C to industry standard, 9.4 mm M12x1, A-coded in accordance with EN 61076-2-101 M8x1, A-coded to EN 61076-2-104 開放式終端
Electrical connection 2, number of pins/wires	2 3 4 5
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V

特性	值
在40°C時的可接受電流負載	0.5 ... 4 A
浪湧強度	0.8 kV
Cable length 1	0.3 ... 30 m
Cable length 2	0.3 ... 30 m
電纜屬性	Suitable for energy chains/robot applications
導體的額定截面	0.14 mm ² 0.25 mm ²
環境溫度	-25 ... 85 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS 不含鹵素 Free of phosphoric acid ester
污染程度	3
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色
Material housing	PA PC TPE-U(PUR)
外殼顏色	黑色