


IO-Link Master USB CDSU-1

料號: 8091509

FESTO



技術參數

特性	值
符合標準	EN 61131-9
Instructions for use	For use with the USB IO-LinkMaster Tool software (available from the Support Portal) for Windows version 7 or higher (32/64 bit).
Input voltage	5 V DC at the USB connection 24 V DC \pm 6 V via external supply
Input current	Max. 2.5 A via external supply Max. 600 mA at the USB connection
Output voltage	24 V DC \pm 10% with USB operation 24 V DC \pm 6 V with external supply (max. input voltage)
極性保護	用於工作電壓連接
短路強度	是
過載承受能力	還未上市
授權	RCM Mark
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
儲藏溫度	-10 ... 75 °C
防護等級	IP20
環境溫度	0 ... 55 °C
產品重量	106 g
通訊協定	IO-Link
IO-Link, protocol	Master V 1.0 Master V 1.1
IO-Link, 通訊模式	COM1 (4,8 kBaud), COM2 (38,4 kBaud), COM3 (230,4 kBaud)
IO-Link, 接口類型	A B, with accessories
IO-Link, 接口數	1
IO-Link, process data width OUT	can be parameterised 0 - 32 bytes
IO-Link, process data width IN	can be parameterised 0 - 32 bytes
IO-Link, 最小周期時間	1,5 ms
IO-Link, memory	2 kByte / Port
IO-Link master, 輸出電流	80 mA with USB operation Max. input current with external supply
Power supply, function	Additional power supply
Power supply, type of connection	插頭插座
Power supply, connection technology	Coaxial
Power supply, note on connection technology	for plugs with outside diameter 5.5 mm/inside diameter 2.1 mm
Power supply, number of pins/wires	2
USB interface, connection technology	USB 2.0 type B mini
USB interface, connection pattern	00995868
USB interface, galvanic isolation	是
Electrical connection for IO-Link®, connection type	插頭插座
Electrical connection for IO-Link®, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for IO-Link®, number of pins/wires	5
IO-Link® electrical connection, occupied pins/wires	3
材料備註	符合 RoHS
Material housing	Anodised wrought aluminium alloy