


連接電纜

NEBC-M12W8-E-15-N-B-LE8

料號: 8094479

FESTO



技術參數

特性	值
基於標準	EN 61076-2-101
授權	c UL us - Listed (OL)
認證核發部門	UL E474609
Cable identification	Without inscription label holder
產品重量	729 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	電纜
Electrical connection 2, connection technology	開放式終端
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
工作電壓範圍 DC	0 ... 30 V
工作電壓範圍 AC	0 ... 30 V
在40°C時的可接受電流負載	2 A
浪湧強度	0.8 kV
Shielding	否
電纜長度	15 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 30 mm
Bending radius, flexible cable installation	>= 30 mm
電纜直徑	6 mm
電纜直徑公差	± 0,2 mm
電纜結構	8x0,25
導體的額定截面	0.25 mm ²
導線末端	Sheath removed
防護等級	IP65 IP67
Note on degree of protection	裝配狀態
環境溫度	-25 ... 90 °C
Ambient temperature with flexible cable installation	-25 ... 90 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	Silver-grey

特性	值
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	黃銅
Material insulation	PP