


接頭

NLFA-D-U14-B1.2-PP-P10

料號: 8104288

FESTO



技術參數

| 特性 | 值 |
|---|---|
| 容器尺寸 | 10 |
| 設計結構 | Tubing mounted via barbed connector |
| 設計 | 直式結構 |
| 尺寸 | Diameter 8 mm |
| Fluid connection | UNF1/4-28 |
| Fluid connection 2 | For tubing internal diameter 1.2 mm |
| 介質 | 流體介質 氣態介質 |
| Note on the medium | Observe resistance of materials that come into contact with media |
| Operating pressure for entire temperature range | -0.075 ... 0.4 MPa |
| 操作壓力的完整溫度範圍 | -0.75 ... 4 bar |
| Operating pressure for entire temperature range | -10.875 ... 58 psi |
| 介質溫度 | 0 ... 35 °C |
| 環境溫度 | 0 ... 35 °C |
| 儲藏溫度 | -20 ... 70 °C |
| 密封原理 | 硬性 |
| 裝配位置 | 任何 |
| 額定鎖緊扭矩 | 15 Ncm |
| 額定擰緊扭矩公差 | ± 15 % |
| 產品重量 | 1.06 g |
| 材料與介質接觸 | PP |
| Material of threaded plug | PA-加強 |
| 材料備註 | 符合 RoHS |
| Food-safe | See Supplementary material information |
| PWIS conformity | VDMA24364 zone III |
| Instructions for use | See application note (available on the Support Portal at festo.com) |