


parallel kit EAMM-U-110-S62-100A-207

Part number: 1217381

★ Core product range

Suitable for electric drives.

FESTO



Data sheet

Feature	Value
Size	110
Assembly position	Any
Gear unit ratio	1:1
Max. speed	5,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	799 kgmm ²
No-load driving torque	0.3 Nm
Transferable torque	25 Nm
Product weight	6,900 g
Interface code, actuator	S62
Interface code, motor in	100A
Materials note	Conforms to RoHS