



Cilindar zaustavljač EFSD-50-PV-M12

Broj artikla: 2942446

FESTO



Tehnički podaci

Svojstvo	Vrijednost
Konstruktivna struktura	Electric stopper cylinder
Veličina	50
Položaj ugradnje	proizvoljno
Prepoznavanje pozicije	s Hallovim sensorom
Klasa korozione otpornosti KBK	1 - niska otpornost na koroziju
Temperatura okoline	-10 ... 60 °C
Temperatura ležaja	-20 ... 60 °C
Relativna vlažnost zraka	0 - 95 % ne kondenzira se
Duljina prigušivanja	17,5 mm
Težina proizvoda	800 g
Maks. frekvencija takta	0,33 Hz
Vrsta pričvršćenja	Sa setom za prilagodbu
Dozvola	RCM Mark
Materijal - napomena	RoHS sukladno
PWIS conformity	VDMA24364 zone III
Material cover	PA PA ojačan
Material seals	NBR
Material housing	Hard anodised wrought aluminium alloy
Material piston rod	visokolegirani čelik, nehrđajući
Material screws	Obloženi čelik
Maks. primljena struja	2 A
Nazivni pogonski napon DC	24 V
Dozvoljena kolebanja napona	+/- 15 %
Vrsta motora	Koračni motor
KC mark	KC-EMV
CE znak (vidi izjavu o sukladnosti)	prema EU-EMV-smjernici
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Mehanička zaštita	IP40
Maks. duljina voda	30 m
Indikacija pogonske spremnosti	LED
Electrical connection for actuator, connection type	Utikači
Electrical connection for actuator, connection technology	M12x1, A-coded u skladu s EN 61076-2-101
Electrical connection for actuator, number of pins/wires	5
Electrical connection for sensor, connection type	Utikači
Electrical connection for sensor, connection technology	M12x1, A-coded u skladu s EN 61076-2-101
Electrical connection for sensor, number of pins/wires	5