



parallel gripper DHPS-35-A

Part number: 1254052

★ Core product range

FESTO



Data sheet

Feature	Value
Size	35
Stroke per gripper jaw	12.5 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	< 0.5 deg
Max. gripper jaw backlash Sz	< 0.02 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	< 0.02 mm
Number of gripper fingers	2
Drive system	pneumatic
Assembly position	Any
Mode of operation	double-acting
Gripper function	Parallel
Gripper force back-up	No
Design structure	Lever guided motion sequence
Guide	Plain-bearing guide
Position detection	For proximity sensor
Total gripping force at 0.6 MPa (6 bar, 87 psi), opening	970 N
Total gripping force at 0.6 MPa (6 bar, 87 psi), closing	910 N
Operating pressure MPa	0.2 ... 0.8 MPa
Operating pressure	2 ... 8 bar 29 ... 116 psi
Max. operating frequency of gripper	2 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	95 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	123 ms
Max. mass per external gripper finger	450 g
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5
Ambient temperature	5 ... 60 °C
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) opening	483 N
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing	450 N
Mass moment of inertia	12.7 kgcm ²
Max. force on gripper jaw Fz static	450 N
Max. torque at gripper Mx static	50 Nm
Max. torque at gripper My static	50 Nm
Max. torque at gripper Mz static	50 Nm
Lubrication interval for guide components	10 Mio SP
Product weight	1,285 g
Mounting type	Internal thread and centring sleeve With through-hole and centring sleeve Optional
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	PA
Material housing	Hard anodised wrought aluminium alloy
Material gripper jaws	High alloy steel, non-corrosive