

limit switch box


SRBC-CA3-YR90-MW-22A-1W-C2P20

Broj artikla: 3482805

★ Osnovni proizvodni program

for electrical feedback and position monitoring of process valves actuated with pneumatic quarter turn actuators.

FESTO



Tehnički podaci

| Svojstvo | Vrijednost |
|--|--|
| Dozvola | c CSA us (OL) |
| CE znak (vidi izjavu o sukladnosti) | prema EU-niski napon-smjernica in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| KC mark | KC-EMV |
| Materijal - napomena | RoHS sukladno |
| Safety Integrity Level (SIL) | SIL 2 |
| Princip mjerenja | mehanički/električno |
| Temperatura okoline | -20 ... 80 °C |
| Uklopni izlaz | s kontaktom |
| Funkcija sklopnog elementa | Prekidač, jedнопolni |
| Maks. izlazna struja AC | 3 A |
| Maks. izlazna struja DC | 3 A |
| Područje pogonskog napona AC | 0 ... 250 V |
| Područje pogonskog napona DC | 0 ... 30 V |
| Električni priključak | Vijčana stezaljka |
| Električni spoj 1, tip konektora | Stezna letva |
| Električni spoj 1, kabelski izlaz | Ravno |
| Električni spoj 1, tehnologija spajanja | Opružna stezaljka |
| Električni spoj 1, broj pinova/žica | 10 |
| Nazivni presjek vodiča koji se može priključiti | 0,25 ... 2,5 mm ² |
| Navojni spoj kabela | M20x1,5 |
| Dozvoljeni promjer kabela | 5 ... 13 mm |
| Dimenzije Š x D x V | 127 mm x 98 mm x 122 mm |
| Priključak za pozicioner i senzor pozicije prema standardu | VDI/VDE 3845 veličina AA 1 |
| Položaj ugradnje | proizvoljno |
| Težina proizvoda | 800 g |
| Boja, kućište | sivo |
| Material housing | Aluminijski tlačni lijev |
| Material seals | NBR |
| Material shaft | visokolegirani čelik, nehrđajući |
| Material screws | visokolegirani čelik, nehrđajući |
| Material blanking plug | PA |
| Material mounting bracket | visokolegirani čelik, nehrđajući |
| Material indicator | PC |
| Information on materials, cable connector | PA |
| Material snap ring | visokolegirani čelik, nehrđajući |
| Material disc | visokolegirani čelik, nehrđajući |
| Material cover cap | PC |
| Indikacija položaja | Žuto/crveno |
| Područje namještanja, snimanje kuta | 0 ... 90 deg |
| Temperatura ležaja | -20 ... 50 °C |

| Svojstvo | Vrijednost |
|--------------------------------|---|
| Mehanička zaštita | IP67 NEMA 4/4X |
| Udarna čvrstoća | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Otpornost na vibracije | Ispitivanje transporta sa stupnjem oštine 2 prema FN 942017-4 i EN 60068-2-6 |
| Klasa korozione otpornosti KBK | 0 - bez otpornosti na koroziju |
| PWIS conformity | VDMA24364 zone III |
| Stupanj onečišćenja | 3 |