

Cuplaj KSE-19-24-D06-D11

Cod: 184264

FESTO

pentru DGE



Fisa tehnica

Caracteristica	valoare
diametru de prindere 1	6 mm
diametru de prindere 2	11 mm
marime de fabricatie	19
pozitie instalare	oricare
numarul max. de turatii	8.000 1/min
momentul de inertie a masei	0,47 kgmm ²
moment de rotatie transferabil	1,5 Nm
greutate produs	12 g
indicatie material	conform RoHS