


# Reductor EMGA-60-A-G3-60P

Cod: 8085344

FESTO



## Fisa tehnica

Caracteristica	valoare
Transmisie flansa	60 mm
Motor cu flansa	60 mm
Joc de rasucire	0,27 deg
tipul reductorului	Reductor in unghi drept
Raport de transmisie	3:1
Viteza maxima de intrare	13.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	14 Nm
Momentul de inertie al angrenajului	0,394 kgcm <sup>2</sup>
Cuplu maxim iesire	22 Nm
Eficienta maxima	95 %
rigiditate la torsiune	2 Nm/arcmin
Greutate produs	1.700 g
Interfata reductor arbore de iesire	60G
Interfata reductor arbore de antrenare	60P
Indicatie material	conform RoHS