


# T形快插接頭 CRQST-1/4-8

料號: 164204

FESTO

360° orientable, male thread with external hexagon.



## 技術參數

特性	值
尺寸	標準
額定尺寸	5 mm
裝配位置	任何
設計	T-形
容器尺寸	1
設計結構	推/拉原理
Operating pressure for entire temperature range	-0.095 ... 1 MPa
操作壓力的完整溫度範圍	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
操作壓力注意事項	Water: max. 0.6 MPa at max. 50°C
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
注意: 操作和嚮導介質	潤滑操作可行
耐腐蝕等級 CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Food-safe	See Supplementary material information
環境溫度	-15 ... 120 °C
產品重量	38 g
輸出數量	2
輸送管線的數量	1
可使用電線	PFAN
安裝類型	External hex A/F 14
氣壓連接, 氣口 1	外螺紋 R1/4
氣壓連接, 氣口 2	For tubing outside diameter 8 mm
Material of threaded plug	高合金鋼, 耐腐蝕
材料備註	符合 RoHS
Material housing	高合金鋼, 耐腐蝕
Material release ring	高合金鋼, 耐腐蝕
Material of tubing seal	FPM
Material of tube retaining claw	高合金鋼, 耐腐蝕
Thrust ring material	高合金鋼, 耐腐蝕