

塑料氣管 PFAN-8X1,25-NT

料號: 197063

FESTO

可用於食品加工行業, 適用溫度高達150° C



技術參數

特性	值
外徑	8 mm
與流量相關的彎曲半徑	110 mm
內徑	5.9 mm
最小彎曲半徑	25 mm
Instructions for use	Tubing without printing
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
操作壓力的完整溫度範圍	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.5 MPa
溫度取決於操作壓力	-0.95 ... 15 bar
Temperature-dependent operating pressure	-13.775 ... 217.5 psi
操作壓力注意事項	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour
Material fire test	UL94 V-0
PWIS conformity	VDMA24364-B2-L
無塵室等級	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information See declaration of conformity
Note on temperature of medium	Water vapour: max. 120°C
環境溫度	-20 ... 150 °C
產品重量視長度而定	0.049 kg/m
氣壓連接	For push-in connector outside diameter 8 mm 用於倒鉤接頭內徑 6 mm 具螺母 用於倒鉤接頭內徑 6 mm
顏色	中性
肖氏硬度	D 60 +5
材料備註	符合 RoHS
Material tubing	PFA