


Adaptive Gripper Finger DHAS-GF-120-U-BU

料號: 3998959

FESTO



技術參數

特性	值
尺寸	120
裝配位置	任何
耐腐蝕等級 CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
RSBP classification to CD-0033	F1a
Food-safe	See Supplementary material information
環境溫度	10 ... 50 °C
產品重量	29 g
材料備註	符合 RoHS
Material clamp jaws	TPE-U(PU)