


# cartridge

## QSPLKG18-8

Part number: 132946

FESTO

With push-in connector, L-form



## Data sheet

| Feature   | Value  |
|---|--|
| Size  | Standard   |
| Nominal size                                    | 5.2 mm   |
| Type of seal on screw-in stud                   | O-ring   |
| Assembly position                               | Any  |
| Design  | L-shape  |
| Container size                                  | 10   |
| Design structure                                | Push/pull principle                                      |
| Operating pressure for entire temperature range | -0.095 ... 1 MPa   |
| Operating pressure complete temperature range   | -0.95 ... 10 bar   |
| Operating pressure for entire temperature range | -13.775 ... 145 psi                                      |
| Maritime classification                         | see certificate  |
| Operating medium                                | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium              | Lubricated operation possible                            |
| Corrosion resistance classification CRC         | 1 - Low corrosion stress                                 |
| PWIS conformity                                 | VDMA24364-B1/B2-L  |
| Ambient temperature                             | -5 ... 60 °C   |
| Product weight                                  | 7.5 g  |
| Mounting type                                   | Mounting pin   |
| Pneumatic connection, port 1                    | Cartridge 18 mm  |
| Pneumatic connection, port 2                    | For tubing outside diameter 8 mm                         |
| Colour of release ring                          | blue   |
| Materials note                                  | Conforms to RoHS   |
| Material housing                                | PA-reinforced  |
| Material release ring                           | POM  |
| Material of tubing seal                         | NBR  |
| Material of tube retaining claw                 | High alloy steel, non-corrosive                          |