


電源插座

NECU-M-PPG5PP-C1-PN

料號: 5195383

FESTO



技術參數

特性	值
通訊協定	PROFINET
授權	c UL us - Recognized (OL)
認證核發部門	UL E328433
附加功能	Fulfils requirements according to AIDA
連接頻率	100
Cable outlet	直的
產品重量	109 g
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, connection technology	Connection pattern PP, coding to pin 2 and 5
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Push-pull with interlock against unintentional pulling
Electrical connection 2, connection technology	壓接式端子
工作電壓範圍 DC	0 ... 24 V
在40°C時的可接受電流負載	16 A
浪湧強度	4 kV
電纜螺紋連接	Pg13.5 hex A/F 22
電纜直徑	9 ... 13 mm
導體的額定截面	0.75 ... 2.5 mm ²
Nominal conductor cross section (AWG)	AWG18 - 13
防護等級	IP65 IP67
Note on degree of protection	裝配狀態
環境溫度	-40 ... 85 °C
儲藏溫度	-40 ... 85 °C
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
Fire test	UL94 V-0
污染程度	3
耐腐蝕等級 CRC	1 - Low corrosion stress
Material housing	Nickel-plated die-cast zinc
外殼顏色	銀
Material seals	NBR TPE-V
Material electrical contact	Nickel-plated and gold-plated copper alloy