



連接電纜

VMPA-KMS2-8-10-PUR

料號: 533506

FESTO

用於多針腳插頭連接至閥島 MPA-S, 適用於電線保護鏈。



技術參數

| 特性 | 值 |
|--|--------------------------------------|
| 基於標準 | DIN 41652 |
| Cable identification | 具配件 |
| 連接頻率 | 50 |
| 產品重量 | 906 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 有角的 |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | Angled |
| Electrical connection 1, connection technology | Sub-D |
| Electrical connection 1, number of pins/wires | 25 |
| Electrical connection 1, occupied pins/wires | 9 |
| Electrical connection 1, type of mounting | 3x M3 screws |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | 電纜 |
| Electrical connection 2, connection technology | 開放式終端 |
| Electrical connection 2, number of pins/wires | 10 |
| Electrical connection 2, occupied pins/wires | 9 |
| 工作電壓範圍 DC | 0 ... 30 V |
| 額定工作電壓 DC | 24 V |
| 容許的電流負載 | 3 A |
| 浪湧強度 | 1 kV |
| 電纜長度 | 10 m |
| 電纜屬性 | Suitable for energy chains |
| 電纜的測試條件 | 視需求的測試條件 |
| Bending radius, fixed cable installation | 21 mm |
| Bending radius, flexible cable installation | 35 mm |
| 電纜螺紋連接 | M20x1,5 |
| 電纜直徑 | 7 mm |
| 電纜結構 | 10x0,25 |
| 導體的額定截面 | 0.25 mm ² |
| 導線末端 | Cut off bluntly |
| 防護等級 | IP65 符合 IEC 60529 |
| Note on degree of protection | 裝配狀態 |
| 環境溫度 | -25 ... 80 °C |
| Ambient temperature with flexible cable installation | -25 ... 80 °C |
| CE 符號 (參見符合的標準) | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| 材料備註 | 符合 RoHS |
| 污染程度 | 3 |
| 耐腐蝕等級 CRC | 2 - Moderate corrosion stress |
| Material cable sheath | TPE-U(PUR) |
| 電纜外套顏色 | 灰色 |

| 特性 | 值 |
|-----------------------------|--------------------------|
| Material housing | PA |
| 外殼顏色 | 灰色 |
| Material of union nut | PA |
| Material seals | CR NBR |
| Material electrical contact | Gold-plated copper alloy |