


連接電纜

NEBU-LE5-K-1-M12G5

料號: 569840

FESTO



技術參數

特性	值
符合標準	EN 61076-2-101
Cable identification	with 2x label holders
產品重量	41 g
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	電纜
Electrical connection 1, connection technology	開放式終端
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Electrical connection 2, type of mounting	Screw lock
工作電壓範圍 DC	0 ... 60 V
工作電壓範圍 AC	0 ... 60 V
在40°C時的可接受電流負載	4 A
浪湧強度	1.5 kV
電纜長度	1 m
電纜屬性	標準
電纜的測試條件	彎折強度符合 Festo 標準, 測試條件根據需求視需求的測試條件 Energy chain: > 5 million cycles, bending radius 75 mm
Bending radius, fixed cable installation	14 mm
Bending radius, flexible cable installation	46 mm
電纜直徑	4.5 mm
電纜直徑公差	± 0,1 mm
電纜結構	5x0,25
導體的額定截面	0.25 mm ²
防護等級	IP65 IP68 IP69K
Note on degree of protection	裝配狀態
Special characteristics	耐油
環境溫度	-25 ... 70 °C
Ambient temperature with flexible cable installation	-5 ... 70 °C
CE 符號 (參見符合的標準)	根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS 不含鹵素 Free of phosphoric acid ester

特性	值
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	灰色
Material housing	TPE-U(PUR)
外殼顏色	黑色
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated copper alloy
Material insulation	PP