



齒輪皮帶軸

ELGC-TB-KF-80-1200

料號: 8062792

FESTO



技術參數

特性	值
傳動齒輪的有效直徑	33.42 mm
工作行程	1,200 mm
尺寸	80
備用行程	0 mm
齒輪皮帶延伸	0.2 %
齒輪皮帶斜度	3 mm
裝配位置	任何
導向	迴圈滾珠軸承導向
設計結構	機電式直線軸 具齒輪皮帶
馬達類型	步進馬達 伺服馬達
測量方式: 位移編碼器	增量式
位置檢測	用於近接感測器 用於電感式感測器
最大加速度	15 m/s ²
最高速度	1.5 m/s
重複精度	±0,1 mm
循環功率	100 %
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
無塵室等級	ISO class 7
防護等級	IP40
環境溫度	0 ... 50 °C
在端點位置的衝擊能量	0.75 mJ
Note on the impact energy it the end positions	At maximum homing speed of 0.01 m/s
轉動面積矩 2nd 度ly	1,370E+03 mm ⁴
轉動面積矩 2nd 度lz	1,660E+03 mm ⁴
最大驅動扭矩	4.178 Nm
最大輸出力Fy	900 N
最大輸出力Fz	2,700 N
Fy for the guide calculation for a service life of 5000 km or 5 million cycles	5,543 N
Fz for the guide calculation for a service life of 5000 km or 5 million cycles	5,543 N
Fy with theoretical service life of 100 km (from a guide perspective only)	20,400 N
Fz with theoretical service life of 100 km (from a guide perspective only)	20,400 N
編碼器電阻的最大遲滯	24.7 N
最大扭矩Mx	59.8 Nm
最大扭矩My	56.2 Nm
最大扭矩Mz	56.2 Nm
Mx for the guide calculation for a service life of 5000 km or 5 million cycles	59.8 Nm

特性	值
My for the guide calculation for a service life of 5000 km or 5 million cycles	56.2 Nm
Mz for the guide calculation for a service life of 5000 km or 5 million cycles	56.2 Nm
Mx with theoretical service life of 100 km (from a guide perspective only)	220 Nm
My with theoretical service life of 100 km (from a guide perspective only)	207 Nm
Mz with theoretical service life of 100 km (from a guide perspective only)	207 Nm
Distance between the slide surface and the centre of the guide	72.5 mm
最大進給力 Fx	250 N
無負載時的驅動扭矩	0.413 Nm
質量慣性扭矩	90.5E+03 mm ⁴
每公尺行程的質量慣性力矩JH	0.1927 kgcm ²
每kg工作負荷的質量慣性力矩JL	2.793 kgcm ²
質量慣性力矩, JO	2.912 kgcm ²
恆定進給	105 mm/U
維修間隔	終身潤滑
運動質量	901 g
0 mm行程時的運動質量	901 g
滑塊重量	272 g
產品重量	12,240 g
0 mm行程時的基本重量	3,500 g
每 10 mm 行程所增加的重量	73 g
Dynamic deflection (load moved)	0.05% of the axis length, max. 0.5 mm
Static deflection (load at standstill)	0.1% of the axis length
Interface code, actuator	T46
Material of end caps	Die-cast aluminium, painted
Material of profile	Anodised wrought aluminium alloy
材料備註	符合 RoHS
Material cover tape	不銹鋼帶
Material drive cover	Die-cast aluminium, painted
Material guide slide	熱處理鋼
Material guide rail	熱處理鋼
Material pulleys	高合金鋼, 耐腐蝕
Material slide	壓鑄鋁
Material toothed belt	氯丁橡膠具玻璃纖維