



連接電纜

NEBC-M8G4-ES-2.5-N-SB-S1G9-RS2-S7

料號: 8086524

FESTO



技術參數

特性	值
通訊協定	RS232
Cable identification	具配件
裝配位置	任何
Electrical connection 1, function	Field device side
Electrical connection 1, design	圓形
Electrical connection 1, connection type	插頭
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	有角的
Electrical connection 2, connection type	插頭插座
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	9
Electrical connection 2, occupied pins/wires	8
Electrical connection 2, type of mounting	2 screws 4-40 UNC
工作電壓範圍 DC	0 ... 24 V
額定工作電壓 DC	24 V
在40°C時的可接受電流負載	4 A
浪湧強度	1.5 kV
Shielding	是
電纜長度	2.5 m
電纜屬性	Suitable for energy chains
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	>= 24 mm
Bending radius, flexible cable installation	>= 47 mm
電纜直徑	4.6 mm
電纜直徑公差	± 0,1 mm
電纜結構	3x0,34
導體的額定截面	0.34 mm ²
防護等級	IP67
Note on degree of protection	IP20 for Sub-D socket 裝配狀態
環境溫度	0 ... 50 °C
Ambient temperature with flexible cable installation	0 ... 50 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	2
Material cable sheath	TPE-U(PUR)
電纜外套顏色	黑色