



馬達電纜

NEBM-H6G4-E-25-Q13N-LE4

料號: 8097205

★ Kernprogramm

FESTO



技術參數

| 特性 | 值 |
|--|--|
| Cable identification | Without inscription label holder |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 有角的 |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, connection technology | Connection pattern H6, coded for the motor |
| Electrical connection 1, number of pins/wires | 4 |
| Electrical connection 1, occupied pins/wires | 4 |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | 電纜 |
| Electrical connection 2, connection technology | 開放式終端 |
| Electrical connection 2, number of pins/wires | 4 |
| Electrical connection 2, occupied pins/wires | 4 |
| 工作電壓範圍 DC | 0 ... 300 V |
| 工作電壓範圍 AC | 0 ... 300 V |
| 在40°C時的可接受電流負載 | 9.5 A |
| 浪湧強度 | 2 kV |
| 電纜長度 | 25 m |
| 電纜屬性 | Suitable for energy chains |
| 電纜的測試條件 | 視需求的測試條件 |
| Bending radius, fixed cable installation | >= 55 mm |
| Bending radius, flexible cable installation | >= 55 mm |
| 電纜直徑 | 7.3 mm |
| 電纜結構 | 4x0,79 |
| 導體的額定截面 | 0.79 mm ² |
| Nominal conductor cross section (AWG) | AWG18 |
| 導線末端 | 導線末端套圈 |
| 防護等級 | IP20 |
| Note on degree of protection | 裝配狀態 |
| 環境溫度 | -25 ... 90 °C |
| Ambient temperature with flexible cable installation | -25 ... 90 °C |
| CE 符號 (參見符合的標準) | 根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK RoHS instructions |
| PWIS conformity | VDMA24364 zone III |
| 材料備註 | 符合 RoHS |
| 污染程度 | 3 |
| 耐腐蝕等級 CRC | 0 - No corrosion stress |
| Material cable sheath | PVC |
| 電纜外套顏色 | 黑色 |
| Material housing | PA |
| 外殼顏色 | 白色 |
| Material insulation | PVC |