


連接電纜

NEBC-R3Z12G20-KH-5-N-SBS-RSG17-ET-S1

料號: 8126916

FESTO



技術參數

特性	值
Cable identification	Without inscription label holder
產品重量	680 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	Plug and socket strip
Electrical connection 1, cable outlet	直的
Electrical connection 1, connection technology	RJ45 and socket strip 12 pins, 2 rows
Electrical connection 1, number of pins/wires	20
Electrical connection 1, occupied pins/wires	14
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	Hybrid plugs
Electrical connection 2, cable outlet	直的
Electrical connection 2, number of pins/wires	17
Electrical connection 2, occupied pins/wires	14
Electrical connection 2, type of mounting	Threaded
工作電壓範圍 DC	0 ... 24 V
額定工作電壓 DC	24 V
在40°C時的可接受電流負載	11.7 A
浪湧強度	6 kV
Shielding	否
電纜長度	5 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
Bending radius, fixed cable installation	≥ 130 mm
Bending radius, flexible cable installation	≥ 130 mm
電纜直徑	8 mm
電纜直徑公差	± 1 mm
電纜結構	4x(1x0,128)+10x0,128
導體的額定截面	0.128 mm ²
防護等級	IP65
Note on degree of protection	裝配狀態
環境溫度	0 ... 40 °C
Ambient temperature with flexible cable installation	0 ... 40 °C
儲藏溫度	-20 ... 70 °C
CE 符號 (參見符合的標準)	根據 EU 低電壓設備指導原則
PWIS conformity	VDMA24364 zone III
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
電纜外套顏色	紅色
Material insulation	PP