

伺服馬達

EMMT-AS-150-LR-HS-R3S

料號: 8148348

FESTO



技術參數

| 特性 | 值 |
|---|---|
| 環境溫度 | -15 ... 40 °C |
| Note on ambient temperature | up to 80°C with derating -1.5%/°C |
| Max. installation height | 4,000 m |
| Note on max. installation height | As of 1,000 m, only with derating of -1.0% per 100 m |
| 儲藏溫度 | -20 ... 70 °C |
| 相對空氣濕度 | 0 - 90 % |
| 符合標準 | IEC 60034 |
| 根據EN60034-1的熱量等級 | F |
| Max. winding temperature | 155 °C |
| 根據EN60034-1的速率等級 | S1 |
| 溫度監控 | Digital motor temperature transmission via EnDat® 2.2 |
| Motor type to EN 60034-7 | IM B5 IM V1 IM V3 |
| 裝配位置 | 任何 |
| 防護等級 | IP21 |
| Note on degree of protection | IP21 for motor shaft without rotary shaft seal IP65 motor shaft with RWDR IP67 for motor housing with connection technology |
| Concentricity, coaxiality, axial runout to DIN SPEC 42955 | N |
| Balance quality | G 2,5 |
| Detent torque | <1.0% of peak torque |
| Storage lifetime under nominal conditions | 20,000 h |
| Interface code, motor out | 150A |
| Electrical connection 1, connection type | Hybrid plugs |
| Electrical connection 1, connection technology | M40x1 |
| Electrical connection 1, number of pins/wires | 15 |
| 污染程度 | 2 |
| 材料備註 | 符合 RoHS |
| 耐腐蝕等級 CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| 耐振動 | 符合 EN 60068-2-6 |
| 耐衝擊 | 符合 EN 60068-2-29 15 g/11 ms to EN 60068-2-27 |
| 授權 | RCM Mark c UL us - Recognized (OL) |
| CE 符號 (參見符合的標準) | 根據 EU-EMV 指導原則 根據 EU 低電壓設備指導原則 in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions |
| 認證核發部門 | UL E342973 |
| 額定工作電壓 DC | 680 V |
| Type of winding switch | Star inside |
| Number of pole pairs | 5 |

| 特性 | 值 |
|---|----------------------------------|
| 靜止扭矩 | 45.5 Nm |
| 額定扭矩 | 29 Nm |
| 峰值 (最大) 扭矩 | 87 Nm |
| 額定擺動速度 | 2,100 1/min |
| 最高速度 | 3,495 1/min |
| Max. mechanical speed | 8,000 1/min |
| 額定馬達功率 | 6,377 W |
| 連續的開路電流 | 23.6 A |
| 額定馬達電流 | 15.4 A |
| 峰值 (最大) 電流 | 49.5 A |
| 馬達恆定 | 1.88 Nm/A |
| Standstill torque constant | 2.23 Nm/A |
| Voltage constant, phase-to-phase | 135.1 mV/min |
| Phase-phase winding resistance | 0.25 Ohm |
| Phase-phase winding inductance | 4.4 mH |
| Winding longitudinal inductivity Ld (phase) | 2.15 mH |
| Winding cross inductivity Lq (phase) | 2.2 mH |
| Electric time constant | 17.1 ms |
| Thermal time constant | 55 min |
| Thermal resistance | 0.39 K/W |
| Measuring flange | 450 x 450 x 30, steel |
| 斷電時轉動慣量總和 | 57.6 kgcm ² |
| 產品重量 | 25,400 g |
| 容許的軸向驅動軸負載 | 274 N |
| 容許的徑向軸負載 | 1,370 N |
| 轉子位置感測器 | Absolute single turn encoder |
| Rotor position sensor, manufacturer designation | ECI 1319 |
| Rotor position sensor, absolute detectable revolutions | 1 |
| Rotary position encoder interface | EnDat 22 |
| Rotary position encoder measuring principle | 電感式 |
| Rotor position sensor, DC operating voltage | 5 V |
| Rotor position sensor, DC operating voltage range | 3.6 ... 14 V |
| Rotor position sensor, position values per revolution | 524,288 |
| 轉子位置編碼器起動裝置 | 19 Bit |
| Rotor position sensor, system accuracy of angle measurement | -65 ... 65 arcsec |
| MTTF, subcomponent | 190 years, rotor position sensor |
| Energy efficiency | ENEFF (CN) / Class 1 |