



three-point gripper HGDD-63-A

Part number: 1163046

FESTO



Data sheet

Feature	Value
Size	63
Stroke per gripper jaw	10 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	≤ 0.1 deg
Max. gripper jaw backlash Sz	≤ 0.05 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.05 mm
Number of gripper fingers	3
Assembly position	Any
Mode of operation	double-acting
Gripper function	3-point
Design structure	Inclined plane guided motion sequence
Position detection	For proximity sensor
Total gripping force at 0.6 MPa (6 bar, 87 psi), opening	1,746 N
Total gripping force at 0.6 MPa (6 bar, 87 psi), closing	1,659 N
Operating pressure	3 ... 8 bar
Operating pressure, sealing air	0 ... 0.5 bar
Max. operating frequency of gripper	≤ 4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	115 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	145 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Protection class	IP65
Ambient temperature	5 ... 60 °C
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) opening	582 N
Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing	553 N
Mass moment of inertia	29 kgcm ²
Max. force on gripper jaw Fz static	2,300 N
Max. torque at gripper Mx static	70 Nm
Max. torque at gripper My static	45 Nm
Max. torque at gripper Mz static	50 Nm
Lubrication interval for guide components	5 Mio SP
Max. mass per external gripper finger	440 g
Product weight	2,175 g
Mounting type	With through-hole and dowel pin With internal thread and dowel pin Optional
Pneumatic connection, sealing air	M5
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	High alloy steel, non-corrosive
Material housing	Smooth-anodised wrought aluminium alloy
Material gripper jaws	Steel, hardened