


solenoid valve

VZWF-B-L-M22C-N12-135-E-2AP4-10-R1

Part number: 1492280

FESTO

force pilot operated, NPT1/2" connection.



Data sheet

| Feature | Value |
|---|---|
| Design structure | Diaphragm valve forced |
| Type of actuation | electrical |
| Sealing principle | soft |
| Assembly position | Magnet standing |
| Mounting type | Line installation |
| Process valve connection | 1/2 NPT |
| Electrical connection | Plug pattern type A to EN 175301-803 Plug to EN 175301-803 Cubic design |
| Nominal size | 13.5 mm |
| Valve function | 2/2 closed, monostable |
| Manual override | None |
| Flow direction | non reversible |
| Medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] Inert gases Mineral oil Water Neutral fluids Other media on request |
| Nominal pressure of process valve | 40 |
| Differential pressure (MPa) | 0 MPa |
| Differential pressure | 0 bar |
| Differential pressure (psi) | 0 psi |
| Characteristic coil data | 110 V AC: 50/60 Hz, pick-up power 19 VA, holding power 16 VA |
| Permissible voltage fluctuation | +/- 10 % |
| Pressure of medium | 0 ... 1 MPa |
| Medium pressure | 0 ... 10 bar |
| Pressure of medium psi | 0 ... 145 psi |
| Max. viscosity | 22 mm ² /s |
| Medium temperature | -10 ... 80 °C |
| Ambient temperature | -10 ... 35 °C |
| Leak rate in accordance with EN 12266-1 | A |
| Flow rate Kv | 2.5 m ³ /h |
| Standard nominal flow rate | 2,660 l/min |
| Switching time on | 130 ms |
| Switching time off | 180 ms |
| Materials note | Conforms to RoHS |
| PWIS conformity | VDMA24364 zone III |
| Material housing | Stainless steel casting |
| Material number for housing | 1.4581 |
| Material seals | EPDM |
| Material screws | High alloy steel, non-corrosive |

| Feature | Value |
|--|---|
| Material number, screw | 1.4301 |
| Product weight | 1,000 g |
| CE mark (see declaration of conformity) | to EU directive low-voltage devices |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment |
| Protection class | IP65 |
| Corrosion resistance classification CRC | 3 - High corrosion stress |