



angle gripper DHWS-25-A-NC

Part number: 1310181

FESTO



Data sheet

Feature	Value
Size	25
Max. replacement accuracy	≤ 0.2 mm
Max. opening angle	40 deg
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.04 mm
Number of gripper fingers	2
Assembly position	Any
Mode of operation	double-acting
Gripper function	Angle
Gripper force back-up	On closing
Design structure	Lever
Position detection	For proximity sensor
Operating pressure	4 ... 8 bar
Max. operating frequency of gripper	≤ 3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	106 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	59 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5
Ambient temperature	5 ... 60 °C
Mass moment of inertia	0.64 kgcm ²
Max. force on gripper jaw Fz static	90 N
Max. torque at gripper Mx static	3.6 Nm
Max. torque at gripper My static	3.6 Nm
Max. torque at gripper Mz static	3.6 Nm
Product weight	265 g
Mounting type	Internal thread and centring sleeve With through-hole and centring sleeve Optional
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover cap	PA
Material housing	Wrought Aluminium alloy Hard anodised
Material gripper jaws	High alloy steel