


cartridge cylinder

EGZ-6-10

Part number: 15034

FESTO

With double-ended male thread on cylinder housing .



Data sheet

| Feature | Value |
|---|--|
| Stroke | 10 mm |
| Piston diameter | 6 mm |
| Cushioning | No cushioning |
| Assembly position | Any |
| Mode of operation | single-acting pushing action |
| Design structure | Piston Piston rod Cylinder barrel |
| Position detection | No |
| Variants | Single-ended piston rod |
| Operating pressure | 2 ... 8 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi) | 14 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 13.9 N |
| Mounting type | with external (male) thread with lock nut Optional |
| Pneumatic connection | M3 |
| Material cover | POM |
| Material seals | TPE-U(PU) |
| Material housing | Brass Nickel plated |
| Material piston rod | High alloy steel |