


push-in sleeve QSH-10-8

Part number: 153259

FESTO

reducing.



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 4.9 mm |
| Assembly position | Any |
| Design | Straight design |
| Container size | 10 |
| Design structure | Push/pull principle |
| Operating pressure for entire temperature range | -0.095 ... 0.6 MPa |
| Operating pressure complete temperature range | -0.95 ... 6 bar |
| Operating pressure for entire temperature range | -13.775 ... 87 psi |
| Temperature-dependent operating pressure | -0.095 ... 1.4 MPa |
| Temperature dependent operating pressure | -0.95 ... 14 bar |
| Temperature-dependent operating pressure | -13.775 ... 203 psi |
| Maritime classification | see certificate |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 80 °C |
| Product weight | 1.3 g |
| Pneumatic connection, port 1 | Push-in sleeve diameter 10 mm |
| Pneumatic connection, port 2 | Push-in sleeve diameter 8 mm |
| Colour of release ring | blue |
| Materials note | Conforms to RoHS |
| Material housing | PBT |