

# solenoid valve

## VZWF-L-M22C-G112-400-V-2AP4-10

Part number: 1492244

FESTO

force pilot operated, G11/2" connection.



### Data sheet

| Feature                                 | Value   |
|---|---|
| Design structure                        | Diaphragm valve<br>forced   |
| Type of actuation                       | electrical  |
| Sealing principle                       | soft  |
| Assembly position                       | Magnet standing   |
| Mounting type                           | Line installation   |
| Process valve connection                | G1 1/2  |
| Electrical connection                   | Plug pattern type A to EN 175301-803<br>Plug<br>to EN 175301-803<br>Cubic design  |
| Nominal size                            | 40 mm   |
| Valve function                          | 2/2 closed, monostable  |
| Manual override                         | None  |
| Flow direction                          | non reversible  |
| Medium                                  | Compressed air in accordance with ISO8573-1:2010 [7:-:-]<br>Inert gases<br>Mineral oil<br>Water<br>Neutral fluids<br>Other media on request |
| Nominal pressure of process valve       | 40  |
| Differential pressure (MPa)             | 0 MPa   |
| Differential pressure                   | 0 bar   |
| Differential pressure (psi)             | 0 psi   |
| Characteristic coil data                | 110 V AC: 50/60 Hz, pick-up power 30 VA, holding power 30 VA  |
| Permissible voltage fluctuation         | +/- 10 %  |
| Pressure of medium                      | 0 ... 1 MPa   |
| Medium pressure                         | 0 ... 10 bar  |
| Pressure of medium psi                  | 0 ... 145 psi   |
| Max. viscosity                          | 22 mm <sup>2</sup> /s   |
| Medium temperature                      | -10 ... 80 °C   |
| Ambient temperature                     | -10 ... 35 °C   |
| Leak rate in accordance with EN 12266-1 | A   |
| Flow rate Kv                            | 22.5 m <sup>3</sup> /h  |
| Standard nominal flow rate              | 23,500 l/min  |
| Switching time on                       | 620 ms  |
| Switching time off                      | 1,140 ms  |
| Materials note                          | Conforms to RoHS  |
| PWIS conformity                         | VDMA24364 zone III  |
| Material housing                        | Cast brass  |
| Material number for housing             | CW617N  |
| Material seals                          | FPM   |
| Material screws                         | High alloy steel, non-corrosive   |

| Feature                                      | Value   |
|--|---|
| Material number, screw                       | 1.4301  |
| Product weight                               | 4,500 g   |
| CE mark (see declaration of conformity)      | to EU directive pressure devices<br>to EU directive low-voltage devices |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment                             |
| Protection class                             | IP65  |
| Corrosion resistance classification CRC      | 1 - Low corrosion stress  |