



proximity sensor SIEN-M30B-NO-S-L

Part number: 150437

FESTO

Inductive, with standard switching distance.



Data sheet

| Feature | Value |
|--|--|
| Conforms to standard | EN 60947-5-2 |
| Authorisation | RCM Mark c UL us - Listed (OL) |
| CE mark (see declaration of conformity) | to EU directive for EMC |
| Materials note | Conforms to RoHS |
| Nominal switching distance | 10 mm |
| Guaranteed switching distance | 8.1 mm |
| Reduction factors | Aluminium = 0.45 Stainless steel, St 18/8 = 0.8 Copper = 0.4 Brass = 0.55 Steel, St 37 = 1.0 |
| Ambient temperature | -25 ... 70 °C |
| Repetition accuracy | 0.5 mm |
| Switch output | NPN |
| Switching element function | Normally closed contact |
| Hysteresis | ≤ 1.1 mm |
| Max. switching frequency | 1,200 Hz |
| Max. output current | 200 mA |
| Voltage drop | ≤ 2 V |
| Short circuit strength | Pulsing |
| Operating voltage range DC | 10 ... 30 V |
| Residual ripple | +/- 20 % |
| Idle current | ≤ 10 mA |
| Polarity protected | for all electrical connections |
| Electrical connection | 3-pin M12x1 Plug |
| Size | M30x1,5 |
| Mounting type | with lock nut |
| Tightening torque | 40 Nm |
| Type of installation | flush |
| Product weight | 100 g |
| Material housing | Brass PA PBTP Chromed-plated |
| Operating status display | Yellow LED |
| Ambient temperature with flexible cable installation | -5 ... 70 °C |
| Protection class | IP67 |
| Surge strength | 0.8 kV |
| PWIS conformity | VDMA24364-B2-L |
| Degree of contamination | 3 |