



# proximity sensor SME-1-S6-C

Part number: 151670

FESTO



## Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions
Materials note	Conforms to RoHS
Measured variable	Position
Measuring principle	Reed magnetic
Ambient temperature	-50 ... 120 °C
Repetition accuracy	0.2 mm
Switch output	with contact, bipolar
Switching element function	Normally open contact
Switch-on time	0.5 ms
Switch-off time	0.03 ms
Max. switching frequency	500 Hz
Max. output current	1 A
Max. contact rating AC	40 VA
Max. contact rating DC	40 W
Voltage drop	$\leq 0$ V
Residual current	0 mA
Short circuit strength	No
Overload withstand capability	Not available
Operating voltage range AC	0 ... 250 V
Operating voltage range DC	0 ... 200 V
Polarity protected	No
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	2
Connector exit direction	axial
Cable length	2.5 m
Cable sheath colour	Grey
Material cable sheath	TPE-S
Mounting type	with accessories
Tightening torque	2.9 Nm
Assembly position	Any
Product weight	130 g
Housing colour	Black
Material housing	Epoxy resin PC PET Steel TPE-O Zinc die-casting

Feature	Value
Ambient temperature with flexible cable installation	-40 ... 120 °C
Protection class	IP67
Insulation voltage	250 V
Surge strength	4 kV
PWIS conformity	VDMA24364-B2-L
Degree of contamination	3