

# compact cylinder


## ADVUL-16-5-P-A

Part number: 156851  
Classic - do not use for new projects

FESTO

For proximity sensing. Piston rod secured against rotation by means of guide rod and yoke plate.

Modern alternatives can be found by entering the first four characters of the type code in the search field.



### Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	16 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Single-ended piston rod
Protection against torque/guide	Guide rod with yoke
Operating pressure MPa	0.15 ... 1 MPa
Operating pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.1 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	90 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	121 N
Mounting type	with through hole with accessories Optional
Pneumatic connection	M5
Material of flange screw	High alloy steel, non-corrosive
Material cover	Wrought Aluminium alloy
Material of dynamic seals	NBR TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	Wrought Aluminium alloy