



Double DNGU-63-PPVAS8

Part number: 158115

FESTO



Datasheet

| Feature | Value |
|--|---------------------------------|
| Mode of operation | Double acting |
| Type of mounting | Screw |
| Form, external | Profile |
| Form piston | Round |
| Form piston rod | Round |
| In accordance with standard ISO | ISO 6431 |
| In accordance with standard VDMA | VDMA 24562 |
| Sensing type | Magnetic |
| Type of cushioning | Adjustable pneumatic cushioning |
| Cushioning length | 23 mm |
| Protection against torsion | None |
| Piston, nominal size | 63 mm |
| Stroke | 0 mm |
| Minimum stroke with B2 = 0 | 1 mm |
| Maximum stroke with B2 = 0 | 2000 mm |
| Piston rod diameter | 20 mm |
| Thread type (piston rod) (KK) | M |
| Thread diameter (metric) | 16 mm |
| Pitch | 1,5 mm |
| Thread length (piston rod) | 32 mm |
| Overall length | 194 mm |
| Operating pressure min. | 0,6 bar |
| Operating pressure max. | 10 bar |
| Minimum ambient temperature | -20 Cel |
| Maximum ambient temperature | 80 Cel |
| Connection type bearing cap (EE) | Thread |
| Thread type (bearing cap) | G |
| Thread diameter (inch) | 3/8 inch |
| Silicone status | Free |
| Connection type cover cap | Thread |
| Thread type (cover cap) | G |
| Thread diameter (inch) | 3/8 inch |
| Effective force (theor.) at 6 bar, adv | .1870 N |

| Feature | Value |
|--|--------------|
| Effect. force (theor.) at 6 bar, retur | n1682 N |
| Maximum buckling load | 190 N |
| Bending load | 48 N |
| Air consumption at 6 bar, advance | 0,22 l/<--> |
| Air consumption at 6 bar, return | 0,2 l/<--> |