

compact cylinder


DMML-16- -P-A-S2

Part number: 158572


FESTO

Non-rotating, for proximity sensing, with elastic cushioning rings in end-positions, wide range of mounting options.

Other stroke lengths on request. Available only in standard stroke lengths 5, 10, 15, 20, 25, 30 mm.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 40 mm
Piston diameter	16 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	double-acting
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Variants	Through piston rod
Protection against torque/guide	Guide rod with yoke
Operating pressure	1 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 80 °C
Tightening torque of the drive mounting	2,5 Nm +10 %
Theoretical force at 6 bar	104 N
Theoretical force at 6 bar, return stroke	104 N
Theoretical force at 6 bar, advance stroke	104 N
Mounting type	Optional with through hole with internal (female) thread
Pneumatic connection	M5
Material cover	Brass
Material seals	TPE-U(PU)
Material housing	Wrought Aluminium alloy Anodised
Material piston rod	High alloy steel, non-corrosive