



Pneumatic DGPI-40--B

Part number: 160902

FESTO



Datasheet

Feature	Value
Mode of operation	Double acting
EU conformity (CE)	CE
Type of mounting	Screw
Form, external	Profile
Form piston	Round
Sensing type	Magnetic
Type of cushioning	Adjustable pneumatic cushioning
Cushioning length	30 mm
Protection against torsion	Guide
Driver principle	Positive-locking (slot)
Guide principle	Slot
Piston, nominal size	40 mm
Stroke	0 mm
Operating pressure min.	1,5 bar
Operating pressure max.	8 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	60 °C
Connection type	Thread
Thread type	G
Thread diameter (inch)	1/4 inch
Silicone status	Free
Connection type connecting thread	Thread
Thread type (connecting thread)	G
Thread diameter (inch)	1/4 inch
Effective force (theor.) at 6 bar	754 N
Air consumption at 6 bar	0,088 L/<->