


mini pressure regulator LR-3,3

Part number: 15717

FESTO

Without sub-base



Data sheet

Feature	Value
Controller function	Output pressure constant with secondary exhaust
Mounting type	Front panel installation
Standard nominal flow rate	150 l/min
Ambient temperature	-10 ... 60 °C
Material housing	POM
Assembly position	Any
Design structure	Diaphragm regulator with secondary exhaust
Operating pressure	10 bar 145 psi
Max. pressure hysteresis	0.3 bar
Pilot pressure	8 bar 120 psi
PWIS conformity	VDMA24364 zone III
Material seals	NBR TPE-A TPE-U(PU)