

# Flat cylinder DZF-32-100-P-A

Part number: 164044

FESTO



## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 100 mm                                                                                     |
| Piston diameter                                              | 32 mm<br>Equivalent diameter                                                               |
| Torsional backlash at piston rod +/-                         | 0.8 deg                                                                                    |
| Cushioning                                                   | Elastic cushioning rings/plates at both ends                                               |
| Mounting position                                            | optional                                                                                   |
| Mode of operation                                            | Double-acting                                                                              |
| Design                                                       | Piston<br>Piston rod                                                                       |
| Position detection                                           | Via proximity switch                                                                       |
| Protection against torque/guide                              | Oval piston                                                                                |
| Operating pressure                                           | 0.1 MPa...1 MPa<br>1 bar...10 bar                                                          |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Ambient temperature                                          | -20 °C...80 °C                                                                             |
| Max. torque for protection against torsion                   | 0.8 Nm                                                                                     |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 415 N                                                                                      |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 483 N                                                                                      |
| Moving mass for 0 mm stroke                                  | 65 g                                                                                       |
| Additional moving mass per 10 mm stroke                      | 9 g                                                                                        |
| Additional weight per 10 mm stroke                           | 24 g                                                                                       |
| Basic weight for 0 mm stroke                                 | 272 g                                                                                      |
| Type of mounting                                             | Either:<br>Via female thread<br>With accessories                                           |
| Pneumatic connection                                         | G1/8                                                                                       |
| Material cover                                               | Wrought aluminium alloy                                                                    |
| Material seals                                               | NBR<br>TPE-U(PU)                                                                           |

| Feature             | Value                        |
|---------------------|------------------------------|
| Material housing    | Aluminium<br>Smooth anodised |
| Material piston rod | High-alloy steel             |