


flat cylinder

DZF-63- -P-A-S6

Part number: 164080

FESTO

Non-rotating, for position sensing, with elastic cushioning rings in end positions. Various mounting options, with or without additional mounting components.



Exemplary representation



Data sheet

| Feature | Value |
|--|---|
| Stroke | 1 ... 320 mm |
| Piston diameter | 63 mm Equivalent diameter |
| Max. angular deflection of piston rod +/- | 0.4 deg |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Mode of operation | double-acting |
| Design structure | Piston Piston rod |
| Position detection | For proximity sensor |
| Variants | Heat resistant seals, max. 120°C |
| Protection against torque/guide | Oval piston |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Operating pressure | 1 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 ... 120 °C |
| Max. torque for protection against rotation | 1.5 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 1,682 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 1,870 N |
| Moving mass with 0 mm stroke | 337 g |
| Additional mass factor per 10 mm of stroke | 25 g |
| Additional weight per 10 mm stroke | 91 g |
| Basic weight for 0 mm stroke | 1,379 g |
| Mounting type | with internal (female) thread with accessories Optional |
| Pneumatic connection | G1/4 |
| Material cover | Aluminium die cast |
| Material seals | FPM |
| Material housing | Aluminium Smooth anodised |
| Material piston rod | High alloy steel |