


Stopper cylinder STAF-32-20-P-A

Part number: 164890

FESTO

With trunnion and built-in flange plate.

This product may not be used within liquid media. Easy retrofitting to a double-acting cylinder is possible.



Data sheet

Feature	Value
Stroke	20 mm
Piston diameter	32 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	single-acting pulling action
Design structure	Piston rod
Position detection	For proximity sensor
Variants	Single-ended piston rod
Operating pressure	1.5 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	2
Ambient temperature	0 ... 60 °C
Impact force	1,000 N
Permissible lateral force during switching operation	550 N
Product weight	540 g
Mounting type	with through hole
Pneumatic connection	M5
Materials note	Free of copper and PTFE
Materials information for cover	Aluminium
Materials information for seals	NBR
Materials information, housing	Aluminium
Materials information for piston rod	High alloy steel, non-corrosive