

MEBH-5/3E-D-1-S-C

Solenoid valve

Data sheet

Part no.: 165624

Page:1

Feature	Data/description
Switching function	5/3-way valve, exhausted in mid-position
Switching function short code	5/3
Function in mid-position (neutral)	Exhausted
Direction of flow reversible	Yes
Operating principle	Slide
Shape of function component	Piston
Type of regulation	Indirect
Control type	Bistable
Type of reset	Mechanical spring
External auxiliary pilot air	Yes
Type of mounting	Screw
Nominal size	8 mm
Operating pressure min.	-0,9 bar
Operating pressure max.	16 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Minimum medium temperature	-5 °C
Maximum medium temperature	50 °C
Min. pilot pressure	3 bar
Pilot pressure max.	10 bar
Type of connection, air supply	Sub-base
Air connection type power port	Sub-base
Type of connection, exhaust	Sub-base
Air connection type aux. pilot air suppl	Sub-base
Air connection type aux. pilot air exhau	Not ducted
Nominal size sub-base connection	Size 1 in accordance with ISO 5599-1
Standard sub-base connection pattern	ISO 5599-1
Standard plug pattern	DIN 43650-1 plug socket
Plug design	A
Actuation/reset	Double solenoid, spring-centred
Manual override	Non-detenting

MEBH-5/3E-D-1-S-C

Solenoid valve

Data sheet

Part no.: 165624

Page:2

Feature	Data/description
Operating status display	No
CT criterion	Free of copper and PTFE
Standard nominal flow rate 1 - 2	1200 l/min
Standard nominal flow rate 2 - 3	1200 l/min
Standard nominal flow rate 1 - 4	1200 l/min
Standard nominal flow rate 4 - 3/5	1200 l/min
Standard nominal flow rate (mid-pos.)	700 l/min
Response time OFF/OVER (dom.)	16 ms
Response time OFF/OVER	55 ms
Voltage type	DC
Nominal voltage	24 V
Power consumption (DC)	2,5 W
Duty cycle, solenoid	100 %
Medium	Compressed air, filtered 50 µm or vacuum
Pilot medium	Compressed air, filtered 5 µm (may be lubricated)
Degree of protection	IP65