

Heavy-duty guide HD-25- -

Part number: 170026


FESTO

Configurable

To configure first add product to the basket.

Depending on configuration, the technical data given on the data sheet and the relevant accessories might not match exactly for this product.

Products to be discontinued. Available until 2009.



Exemplary representation

Data sheet

~ConfIndependentDatasheet

Feature	Value
Size	25
Stroke	10 ... 2,160 mm
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Guide axis without drive unit
Max. speed	3 m/s
Corrosion resistance classification CRC	0
Ambient temperature	-10 ... 60 °C
Max. force Fy	5,400 N
Max. force Fz	5,600 N
Max. torque Mx	260 Nm
Max. torque My	415 Nm
Max. torque Mz	400 Nm
Moving mass	1,780 g
Moving mass with 0 mm stroke	1,780 g
Additional weight per 10 mm stroke	116 g
Basic weight for 0 mm stroke	3,600 g
Materials information for guide component	Steel
Materials information, housing	Wrought Aluminium alloy Anodised