

# Guided drive DFM-16-10-P-A-KF

Part number: 170907

FESTO



## Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	10 mm
Piston diameter	16 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Impact energy in end positions	0,15 Nm
Max. force Fy	389 N
Max. force Fy static	415 N
Max. force Fz	389 N
Max. force Fz static	415 N
Max. moment Mx	8.95 Nm
Max. torque Mx static	9.55 Nm
Max. moment My	3.89 Nm
Max. torque My static	4.15 Nm
Max. moment Mz	3.89 Nm
Max. torque Mz static	4.15 Nm
Max. permissible torque load Mx as a function of stroke	2.19 Nm

<b>Feature</b>	<b>Value</b>
Max. effective load dependent upon stroke at defined distance xs	45 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	90 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Moving mass	212 g
Product weight	426 g
Centre of gravity of moving mass as a function of stroke	13.4 mm
alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel