



Round cylinder DSAG-16- -P-A-Q-S2

Part number: 176275

FESTO

End cap with threaded lug, with square, through piston rod
This product is only available if ordered from Festo Korea Co. Ltd.



Exemplary representation

Data sheet

Feature	Value
Stroke	1 ... 250 mm
Piston diameter	16 mm
Cushioning	P: Flexible cushioning rings/plates at both ends
Protection against torque/guide	Square guide
Operating pressure	1 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	103.7 N
Theoretical force at 6 bar, advance stroke	120.6 N
Moving mass with 0 mm stroke	35 g
Additional weight per 10 mm stroke	4.9 g
Basic weight for 0 mm stroke	56 g
Additional mass factor per 10 mm of stroke	2.2 g
Pneumatic connection	M5
Materials information for cover	Wrought Aluminium alloy
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	High alloy steel, non-corrosive
Materials information for piston rod	High alloy steel, non-corrosive