

# Clevis foot CRLNG-100

Part number: 161845

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Size   | 100  |
| Based on standard                                  | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)  |
| Mounting position                                  | optional   |
| Corrosion resistance class CRC                     | 4 - Very high corrosion stress   |
| LABS (PWIS) conformity                             | VDMA24364-B2-L   |
| Suitability for the production of Li-ion batteries | Metals with more than 1% copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Ambient temperature                                | -40 °C...80 °C   |
| Product weight                                     | 915 g  |
| Note on materials                                  | RoHS-compliant   |
| Material mounting                                  | Electropolished<br>High-alloy steel  |
| Material bearing                                   | Polymer  |