


Vacuum generator VADMI-200-N

Part number: 162533

FESTO



Data sheet

| Feature | Value |
|-------------------------------|---|
| Nominal size, Laval nozzle | 2 mm |
| Grid dimension | 22 mm |
| Silencer design | Closed |
| Mounting position | optional |
| Ejector characteristic | High vacuum |
| Grade of filtration | 40 µm |
| Manual override | Non-detenting |
| Integrated function | Electric ejector pulse valve Flow control Electric on-off valve Filter Check valve Vacuum switch |
| Measured variable | Relative pressure |
| Measuring principle | Piezoresistive |
| Switching element function | N/O contact |
| Switching function | Threshold value comparator |
| Valve function | Closed |
| Reverse polarity protection | For all electrical connections |
| Display type | LED |
| Setting range hysteresis | -50 kPa...-5 kPa -0.5 bar...-0.05 bar -7.25 psi...-0.725 psi |
| Setting options | Potentiometer |
| Switching status indication | Optical |
| Setting range threshold value | -90 kPa...0 kPa -0.9 bar...0 bar -13.05 psi...0 psi |
| Operating pressure | 0.2 MPa...0.8 MPa 2 bar...8 bar 29 psi...116 psi |
| Max. vacuum | 85 % |
| Nominal operating pressure | 0.6 MPa 6 bar 87 psi |

| Feature | Value |
|--|--|
| Max. overload pressure | 5 bar |
| Air supply time at nominal operating pressure with ejector pulse | 0.15 s |
| Operational voltage range DC | 21.6 V...26.4 V |
| Duty cycle | 100% |
| Switching output | NPN |
| Approval | RCM trademark c UL us - Recognized (OL) |
| CE mark (see declaration of conformity) | To EU EMC Directive |
| CE marking (see declaration of conformity) | To UK instructions for EMC |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | 0 °C...60 °C |
| Degree of protection | IP65 |
| Ambient temperature | 0 °C...50 °C |
| Product weight | 360 g |
| Pressure measuring range | 0 MPa...0.1 MPa 0 bar...1 bar 0 psi...14.5 psi |
| Electrical connection | 4-pin M8x1 Plugs |
| Type of mounting | Either: With through-hole Via female thread |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 3 | Integrated silencer |
| Vacuum connection | G3/8 |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material receiver nozzle | Brass, nickel-plated |
| Material filter | PA |
| Material filter housing | PC |
| Material housing | Wrought aluminium alloy |
| Material silencer | PE POM |
| Material piston | POM |
| Material transmitter nozzle | Nickel-plated brass |