



LFR-M2-G1/2-E10UG

Filter regulator

Feature	Data/description
Size	2
Series	M
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Filter regulator with pressure gauge
Max. condensate volume	54 ml
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Pressure control range	0 - 10 bar
Inlet pressure 1	0 - 17 bar
Standard nominal flow rate	4.500 l/min
Operating medium	Compressed air
Storage temperature	-10 - 60 °C
Medium temperature	-10 - 80 °C
Ambient temperature	-10 - 80 °C
Product weight	1.219 g
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Materials note	Contains PWIS substances



Data sheet

Part no.: **179636**

Page:2

LFR-M2-G1/2-E10UG

Filter regulator

Feature	Data/description
Materials information, housing	Zinc die-casting
Materials information for bowl	Zinc die-casting