


electrical interface CPV18-GE-DI01-8

Part number: 165813
Product to be discontinued

FESTO



Data sheet

Feature	Value
CP string extension	Yes 16 inputs 8 outputs (or 16 valves)
Fieldbus interface	Optional - Socket and plug, M12x1, 5-pin, B coded - Sub-D, 9-pin, socket
Device-specific diagnostics	via device-relating diagnosis (DPV0) Missing module on CP string extension Short-circuit / overload, outputs Undervoltage, outputs Undervoltage, sensor supply power Undervoltage, valves
Communication types	Cyclical communication
Configuration support	DDB file and bitmaps
Maximum number of solenoid coils with string extension	32
Max. number of solenoid coils	16
Polarity protected	for all electrical connections
Baud rate	9,6 kBaud ... 12 Mbaud Automatic detection
Operating voltage range DC	20.4 ... 26.4 V
Maximum number of outputs	8 (16 solenoid coils eliminated)
Maximum number of inputs	16
Nominal operating voltage DC	24 V
Power failure buffering	10 ms
Residual ripple	4 V _{ss}
Current consumption at nominal operating voltage, load	Depending on valve type
Current consumption at nominal operating voltage	Electronics: ≤ 100 mA Sensor supply power: depends upon sensor
Storage temperature	-20 ... 70 °C
Protection class	IP65
Ambient temperature	-5 ... 50 °C
Authorisation	c UL us - Recognized (OL)
Addressing range	1 ... 125 Adjustment via switch module
Fieldbus certification	PNO
Electrical isolation, fieldbus interface	Optocoupler
Bus-specific LED display	BUS: communication and configuration errors
Product-specific LED display	12/14: switching status at valves POWER: operating voltage for electronics and load supply
Product ID	Product range: 4: valves
Material cover	PA-reinforced
Material seals	CR NBR
Material housing	Aluminium die cast
Materials note	Conforms to RoHS