


# servo motor EMMS-AS-70-S-LV-RRB-S1

Part number: 1704748

FESTO

Without gear unit.



## Data sheet

Feature	Value
Ambient temperature	-40 ... 40 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class according to EN 60034-1	S1
Temperature monitoring	PTC resistor
Protection class	IP65
Electrical connector system	Plug
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorisation	RCM Mark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices
Nominal operating voltage DC	360 V
Nominal voltage DC	360 V
Type of winding switch	Star inside
Number of pole pairs	4
Standstill torque	1.64 Nm
Nominal torque	1.37 Nm
Peak torque	5 Nm
Nominal rotary speed	6,600 1/min
Max. speed	8,070 1/min
Nominal motor power	945 W
Nominal motor current	2.64 A
Peak current	11 A
Motor constant	0.518 Nm/A
Voltage constant, phase-to-phase	31.54 mVmin
Phase-phase winding resistance	4.9 Ohm
Phase-phase winding inductance	8.45 mH
Overall mass moment of inertia at power take-off	0.46 kgcm <sup>2</sup>
Product weight	2,390 g
Permissible axial shaft load	75 N
Permissible radial shaft load	150 N
Rotor position sensor	Resolver
Rotary position encoder interface	SIN/COS analogue signal
Rotary position encoder measuring principle	Inductive
Brake holding torque	2 Nm
Operating voltage DC for brake	24 V
Power consumption, brake	11 W
Mass moment of inertia of brake	0.07 kgcm <sup>2</sup>
Switching cycles, holding brake	10 million idle actuations (without friction work)
MTTF, subcomponent	80 years, rotary position encoder 1769 years, holding brake
MTTFd, subcomponent	160 years, rotary position encoder