

Guided drive DFM-20-80-P-A-KF

Part number: 170920

FESTO



Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	80 mm
Piston diameter	20 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Position detection	Via proximity switch
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Impact energy in end positions	0,2 Nm
Max. force Fy	817 N
Max. force Fy static	1020 N
Max. force Fz	817 N
Max. force Fz static	1020 N
Max. moment Mx	23.69 Nm
Max. torque Mx static	29.58 Nm
Max. moment My	15.11 Nm
Max. torque My static	18.87 Nm
Max. moment Mz	15.11 Nm
Max. torque Mz static	18.87 Nm
Max. permissible torque load Mx as a function of stroke	3.36 Nm

Feature	Value
Max. effective load dependent upon stroke at defined distance xs	86 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	141 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188 N
Moving mass	584 g
Product weight	1310 g
Centre of gravity of moving mass as a function of stroke	50.9 mm
alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel