


LFM-M1-G1/4-BT

Fine filter

| Feature | Data/description |
|----------------------------------|---|
| Size | 1 |
| Series | M |
| Assembly position | Vertical +/- 5° |
| Grade of filtration | 1 µm |
| Filter efficiency | 99,9999 % |
| Condensate drain | manual rotary |
| Design structure | Fibre filter |
| Max. condensate volume | 10,25 cm ³ |
| Bowl guard | Plastic guard |
| Inlet pressure 1 | 0 - 17 bar |
| Standard nominal flow rate | 140 l/min |
| Operating medium | Compressed air |
| Storage temperature | -10 - 60 °C |
| Medium temperature | -10 - 60 °C |
| Residual oil content | 0,5 mg/m ³ |
| Ambient temperature | -10 - 60 °C |
| Mounting type | Optional Line installation with accessories |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Materials note | Contains PWIS substances |
| Materials information for filter | Boron silicate fibre |
| Materials information, housing | Zinc die-casting |

**LFM-M1-G1/4-BT****Fine filter**

| Feature | Data/description |
|--------------------------------|------------------|
| Materials information for bowl | Zinc die-casting |