



## LFM-M1-G1/4-XT

### Micro filter

Feature	Data/description
Size	1
Series	M
Assembly position	Vertical +/- 5°
Filter efficiency	0,9999 %
Condensate drain	manual rotary
Design structure	Active carbon filter
Max. condensate volume	10,25 cm <sup>3</sup>
Bowl guard	Plastic guard
Inlet pressure 1	0 - 17 bar
Flow characteristics (graph)	[ Diagramm ]
Standard nominal flow rate	210 l/min
Operating medium	Filtered, unlubricated compressed air, 0.01 µm filtration
Medium temperature	-10 - 30 °C
Residual oil content	0,003 mg/m <sup>3</sup>
Ambient temperature	-10 - 30 °C
Mounting type	Optional Line installation with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials note	Contains PWIS substances
Materials information for filter	Active carbon
Materials information, housing	Zinc die-casting
Materials information for bowl	Zinc die-casting